

# Pleated Filters and Filter Cartridge Kits



## Contact Information:

Parker Hannifin Corporation  
**Racor Division/Village Marine Tec.**  
2000 W. 135th St.  
Gardena, CA 90249

phone 310 516 9911  
fax 310 538 3048  
racor@parker.com  
www.villagemarine.com

[www.parker.com/racor](http://www.parker.com/racor)



The Village Marine Tec. line of pleated filters are designed specifically for the RO watermaker industry and are superior to wound or polyspun cartridges to give you a longer filter life as well as increasing flow rates and keeping cartridge size down.

Available in a wide arrange of sizes and micron ranges to ensure that every type of watermaker filter need is taken care of. Stock sizes fit most standard filter housings, if the size you need is not shown please contact us with the dimensions required.

Single use Cleaning and Preservative Cartridge Kits are designed specifically for small RO Systems. The Cartridges allow for easy and effective membrane maintenance.

The Cleaning and Preservative Cartridge Kits eliminate the trouble and mess of measuring powdered chemicals and ensuring correct chemical concentrations. The Chemical cartridges fit directly into 2.5" x 10" housings and contain the correct amount of chemical for a single use.

ENGINEERING YOUR SUCCESS.

# Pleated Filters and Filter Cartridge Kits

## Features:

### Pleated Filters

- Polypropylene pleated construction
- Longer service life over wound or polyspun cartridges
- Easily cleaned and reused
- Chemically compatible with a wide range of alkalies, most acids and saline solutions
- 0.5, 1, 5, and 20 micron ranges available
- Pliable plastisol ends ensures filter seal to eliminate bypass
- High packing density reduces filter size while keeping flow rates up
- Filter bands on large diameter elements keep filter shape during system pulsations

### Pleated Sediment Elements

Part Number	Microns	Filter Area ft <sup>3</sup> /m <sup>3</sup>	Diameter inch/cm	Length inch/cm
33-0118	20	10/0.93	2.75/7	9.75/25
33-0117	5	10/0.93	2.75/7	9.75/25
33-0053	20	18/1.67	4.5/11.4	9.75/25
33-0052	5	18/1.67	4.5/11.4	9.75/25
33-0020	20	30/2.79	8.63/22	7.75/20
33-0005	5	30/2.79	8.63/22	7.75/20
33-0058	20	35/3.25	4.5/11.4	20/51
33-0057	5	35/3.25	4.5/11.4	20/51
35-0020	20	35/3.25	6.12/15.5	11.9/30
35-0001	5	35/3.25	6.12/15.5	11.9/30
33-0172	100	100/9.29	8.63/22	24.3/62
33-2100	20	100/9.29	8.63/22	24.3/62
33-5100	5	100/9.29	8.63/22	24.3/62
33-1100	1	100/9.29	8.63/22	24.3/62
33-1105	0.5	100/9.29	8.63/22	24.3/62

### Filter Cartridge Kits

- Cartridge with Blue stripe contains cleaner #1, a biological cleaner to remove algae, fungi and bacteria
- Cartridge with Red stripe contains cleaner #2, an acidic cleaner to remove scale from the membrane
- Cartridge with Green stripe contains the preservative. This chemical is used for pickling the membranes
- Cartridges are capable of being used in any housing that takes a standard 2.5" (64mm) x 10" (254mm) filter cartridges

### Carbon Flushing Filters

Part Number	Diameter inch/cm	Length inch/cm
33-0311	2.75/7	9.75/25
33-0315	4.5/11.4	9.75/25
33-0083	4.5/11.4	20/50.8

### Cartridge Filter Kits

Description	Part Number	Contents
Cleaning Kit	85-0102	One Blue stripe cleaner #1 plus One Red stripe cleaner #2
Preservation Kit	85-0103	Two Green stripe preservative

To maintain peak performance always use genuine Parker-Racor/Village Marine Tec. replacement parts. We reserve the right to change our specifications or standards without notice.

PROSEP FILTER SYSTEMS LTD  
Unit G19  
River Bank Way  
Lowfields Business Park  
Elland  
West Yorkshire  
HX5 9DN

**Tel: 01422 377367**

**Fax: 01422 377369**

Email: [enquiries@prosep.co.uk](mailto:enquiries@prosep.co.uk)

[www.prosep.co.uk](http://www.prosep.co.uk)

**Map and Directions to Prosep Filters Limited**



Leave M62 at Junction 24.

At roundabout adjacent to Cedar Court Hotel take 2nd exit onto dual carriageway (A629), signposted Halifax.

Take 1st exit slip road.

At roundabout at end of sliproad, take 3rd exit off.

This is the entrance to Lowfields Business Park.

Proceed straight over 1st roundabout.

At next roundabout take 2nd exit onto River Bank Way - Prosep Filters can be found on the left after the S-bend.

[Link to Google Maps](#)